

16 Slice

NON CON ABD IN 5S/Abdomen

- 1 Surview, AP
- 2 Body, NON-CONS/LOC, Hel...
- 3 Recon, THIN
- 4 MPR, COR, Coronal

Scan Type: Body
Clinical Application: none

Label: NON-CONS/LOC

Length: 355.0

Direction: In Out

Thickness: 5 mm

Increment: 2.5 mm

kV: 120

mAs/Slice: 300

Evolving

Images: 141 CTDI: 20.0mGy
Time: 13.113 DLP: 787.2mGy*cm

NON CON ABD IN 5S/Abdomen

- 1 Surview, AP
- 2 Body, NON-CONS/LOC, Hel...
- 3 Recon, THIN
- 4 MPR, COR, Coronal

Label: THIN

Start offset: 1.5

End: *

Length: 352.0

FOV: 400 mm

Thickness: 2 mm

Increment: 1.0 mm

Filter: Sharp (C)

Enhancement: 0.0

Window C: 50 W: 450

Center X: 0 Y: 0

Matrix: 512 AF SP

NON CON ABD IN 5S/Abdomen

- 1 Surview, AP
- 2 Body, NON-CONS/LOC, Hel...
- 3 Recon, THIN
- 4 MPR, COR, Coronal

Label: COR

Orientation: Sagittal Coronal Axial

Length: 400.0

No. of Images: 159

Thickness: 5.0 mm

Increment: 2.5 mm

Angle: -90.0

Window C: 50 W: 450

Render Mode: Average

64 Slice

NON CONS IN 5S/Abdomen

- 1 **Surview, AP**
- 2 **Body, NON CON 5S, Helical**
- 3 Recon, THINS
- 4 MPR, CORONALS, Coronal

Scan Type: Body
Clinical Application: none
Label: NON CON 5S
Length: 355.0
Direction: In Out
Thickness: 5 mm
Increment: 2.5 mm
kV: 120
mAs/Slice (mA): 335 496

Evolving

Images: 141 CTDI: 19.7mGy
Time: 7.179s DLP: 837.2mGy*cm

NON CONS IN 5S/Abdomen

- 1 **Surview, AP**
- 2 **Body, NON CON 5S, Helical**
- 3 Recon, THINS
- 4 MPR, CORONALS, Coronal

Resolution: standard
Collimation: 64x0.625
Pitch: 1.11
Rotation time: 0.75 sec
FOV: 400 mm
Filter: Sharp (C)
Enhancement: 0.0
Window C: 50 W: 450
Center X: 0 Y: 0
Matrix: 512
DOM: no

Dose Right ACS Adaptive Filter
 SP Filter

NON CONS IN 5S/Abdomen

- 1 **Surview, AP**
- 2 **Body, NON CON 5S, Helical**
- 3 **Recon, THINS**
- 4 MPR, CORONALS, Coronal

Label: THINS
Start offset: 2.0
End: *
Length: 350.0
FOV: 400 mm
Thickness: 2 mm
Increment: 1.0 mm
Filter: Sharp (C)
Enhancement: 0.0
Window C: 50 W: 450
Center X: 0 Y: 0
Matrix: 512 AF SP

NON CONS IN 5S/Abdomen

- 1 **Surview, AP**
- 2 **Body, NON CON 5S, Helical**
- 3 Recon, THINS
- 4 **MPR, CORONALS, Coronal**

Label: CORONALS
Orientation: Sagittal Coronal Axial
Length: 400.0
No. of Images: 159
Thickness: 5.0 mm
Increment: 2.5 mm
Angle: -90.0
Window C: 50 W: 450
Render Mode: Average